Common Sockets

CSM_common_sockets_DS_E_3_16

A Wide Variety of Square and **Round Sockets in Front-mounting** and Back-mounting Models

- Models available with finger protection.
- Hold-down Clips and Short Bars for PYFZ/PYF Sockets are also available.
- New screwless models available.



For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

Ordering Information

Square Sockets


Model	P2RF (front-mounting), page 8			P2R (back-mounting), pages 11 and 12			P7TF (front-
Number of pins				Solder terminals	PCB terminals		mounting), page 12
	P2RF-05 Approx. 27 g	P2RFZ-05-E Approx. 30 g	P2RF-05-E* Approx. 38 g	P2R-05A Approx. 5 g	P2R-05P Approx. 5 g	P2R-057P Approx. 5.5 g	P7TF-05 Approx. 28 g
5 pins		H.C.					
8 pins	P2RF-08 Approx. 33 g	P2RFZ-08-E Approx. 38 g	P2RF-08-E* Approx. 38 g	P2R-08A Approx. 5 g	P2R-08P Approx. 5 g	P2R-087P Approx. 5.5 g	_

Note: 1. The structure of □-E models provides finger protection. Round terminals cannot be used. Use forked crimp terminals.

2. To remove the Relay, pull the lever on the Socket with your fingers supporting the lever and the opposite side of the Relay case, and jiggle the Relay.

★ Use a #1 Phillips screwdriver to tighten the screws on this Socket.

PTF (Unit: mm)



Note: If you use the PTF08A, PTF08A-E, or PT08 with an LY1 Relay, connect the following terminal pairs: 1-2, 3-4, and 5-6 (for usage at 10 A or higher).